



# Premium test stand for laboratory applications

#### **Features**

- Motorised test stand for tension an compression tests
- Table-top design for comfortable operation
- Robust design for durable use
- Easy-to-access safety switch-off
- Upper and lower end point, can be set individually
- · Automatic or manual operation mode
- Can be used for force gauges up to 500 N (e.g. SAUTER FH-S, not included, for details see page 12)

#### **Technical data**

- Maximum tensile and compressive force: 500 N
- Maximum travel length: 300 mm
- Speed accuracy: 2 % of [Max]
- Net weight approx. 25 kg

#### Accessories

- Digital length measuring device, measuring range 300 mm, readout 0,01 mm, details see page 35, SAUTER LB 300-2.
- Mounting the length measuring device onto a SAUTER test stand at the factory, SAUTER LB-A02
- Force-time data transfer software for graphical representation on the PC and data transfer to Microsoft Excel®, SAUTER AFH FAST
- Force-displacement data transfer software with graphic display of the measurement process, SAUTER AFH FD







Model	Measuring range	Speed range	Max. travelling	Dimensions	
	[Max]		distance	W×D×H	
SAUTER	N	mm/min	mm	mm	
TVO 500N300.	500	15-300	300	236×428×570	

# **SAUTER Pictograms:**





#### Adjusting program (CAL):

For quick setting of the balance's accuracy. External adjusting weight required.



# Control outputs

#### (optocoupler, digital I/O):

to connect relays, signal lamps, valves, etc.



#### Rechargeable battery pack:

rechargeable set.



PEAK

#### Calibration block:

Peak hold function:

measuring process.

standard for adjusting or correcting the measuring device.



#### Analogue interface:

to connect a suitable peripheral device for analogue processing of the measurements.



#### Mains adapter:

230V/50Hz in standard version for EU. On request GB, AUS or USA version available.



#### Statistics:

using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



### Power supply:

Integrated, 230V/50Hz in EU. More standards e.g. GB, AUS or USA on request.



### Motorised drive:

The mechanical movement is carried out by a electric motor.



SCAN

# Scan mode:

Push and Pull:

continuous capture and display of measurements.

capturing a peak value within a



PRINT

# PC Software:

Printer:

to transfer the measurements from the device to a PC.

a printer can be connected to the

device to print out the measurements.



Motorised drive: The mechanical movement is carried out

by a synchronous motor (stepper).

DAkkS calibration possible:

is shown in days in the pictogram.



#### Length measurement:

and compression forces.

captures the geometric dimensions of a test object or the movement during a test process.

the measuring device can capture tension



### GLP/ISO record keeping:

of measurements with date, time and serial number. Only with SAUTER printers.



#### Fast-Move:

the total length of travel can be covered by a single lever movement.



MEMORY

#### Focus function:

Internal memory:

to save measurements

in the device memory.

increases the measuring accuracy of a device within a defined measuring range.



#### Measuring units:

Weighing units can be switched to e.g. non-metric at the touch of a key. Please refer to website for more details.



# Measuring with tolerance range

(limit-setting function): Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model





DAkkS

+3 DAYS

#### Factory calibration:

The time required for factory calibration is specified in the pictogram.

The time required for DAkkS calibration



#### Data interface RS-232:

bidirectional, for connection of printer and PC.



Resets the display to "0".



### Package shipment:

The time required for internal shipping preparations is shown in days in the pictogram.



# Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram.



#### Data interface USB:

To connect the balance to a printer, PC or other peripheral devices.



## Data interface Infrared:

To transfer data from the balance to a printer, PC or other peripheral devices.



# **Battery operation:**

Ready for battery operation. The battery type is specified for each device.

